



kreon installation manual

technics & dimensions



name	reference	ØA	B	C
Size 80 Rounded glare preventer	KR70673x	51,5	54	
Size 120 Rounded glare preventer	KR70683x	95	90	
Size 80 Straight glare preventer	KR70672x	51,5		30
Size 120 Straight glare preventer	KR70682x	95		40

1. installation



Push the legs of the glare preventer in the three openings of the glare snoot in the assembled Diapason or ATO untill click

To install optional lenses in the glare preventer consult installation manual KR8166002148