


# kreon installation manual

## technics & dimensions




name	reference	voltage	power	LxW	D
Prologe on-kagi fixed lvl 2	KR95403X-XXXX-XX-XX	24 V	9,8W	144x45	45
Holon on-kagi fixed lvl 2	KR95453X-XXXX-XX-XX	24 V	9,8W	144x45	45

Please make sure the main voltage is disconnected before proceeding!




### 1. preparation

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.




The gear contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person



### 2. installation


See manual KR8000002364 for installation of the main profile



Please note that these fixtures are only suitable for profiles on the first level of your Kagi structure. For fixtures of the second level please see manual KR8000002358.



✗ NOT OK




✓ OK


# kreon installation manual

## 3. installation


Remove the louvre



Open the sliders by turning the screw, using the tool from KR754911, or a hex key, until you feel the blocking mechanism




Stop when you feel the blocking mechanism, make sure the sliders are fully open




## 4. installation


Push the fixture slightly deeper into the housing



Until it clicks into it's secondary position




Place the fixture over the profile




## 5. installation


Push the fixture back up into the housing



Close the sliders using the tool, make sure no cables are pinched




Make sure the sliders are fully closed




# kreon installation manual

## 5. installation


Insert the louvre





In case of a blind profile, insert the gasket.



Result



# kreon light source information

Fixture reference	LED reference	Energy Efficiency Class	QR-code	EPREL link
KR95403X-9027-XX-XX KR95453X-9027-XX-XX	KR7000104033	F		<a href="https://eprel.ec.europa.eu/qr/1207233">https://eprel.ec.europa.eu/qr/1207233</a>
KR95403X-9030-XX-XX KR95453X-9030-XX-XX	KR7000104034	G		<a href="https://eprel.ec.europa.eu/qr/1207509">https://eprel.ec.europa.eu/qr/1207509</a>